

# Pressure gauge PAGL-HP3-63-60-G14

Part number: 1166938

**FESTO**



## Data sheet

| Feature                             | Value                                                                                                                      |
|-------------------------------------|----------------------------------------------------------------------------------------------------------------------------|
| Indicating range                    | 0 bar...60 bar<br>0 MPa...6 MPa<br>0 psi...870 psi                                                                         |
| Conforms to standard                | EN 837-1                                                                                                                   |
| Nominal size of pressure gauge      | 63                                                                                                                         |
| Explosion protection                | The information in the certificate must be observed!<br>Zone 1 (ATEX)<br>Zone 2 (ATEX)<br>Zone 21 (ATEX)<br>Zone 22 (ATEX) |
| Design                              | Bourdon tube pressure gauge                                                                                                |
| Type of mounting                    | In-line installation                                                                                                       |
| Operating medium                    | Inert gases<br>Neutral fluids                                                                                              |
| Note on operating and pilot medium  | No acetylene<br>No oxygen                                                                                                  |
| Operating pressure                  | 0 MPa...6 MPa<br>0 bar...60 bar<br>0 psi...870 psi                                                                         |
| Alternating load factor             | 0.66                                                                                                                       |
| Measurement accuracy class          | 1.6                                                                                                                        |
| Degree of protection                | IP65                                                                                                                       |
| Storage temperature                 | -40 °C...70 °C                                                                                                             |
| Media temperature                   | 0 °C...60 °C                                                                                                               |
| Ambient temperature                 | 0 °C...60 °C                                                                                                               |
| Note on materials                   | RoHS-compliant                                                                                                             |
| Position of connection              | Centred, rear side                                                                                                         |
| Pneumatic connection                | G1/4                                                                                                                       |
| Material in contact with the medium | Brass                                                                                                                      |
| Material screwed plug               | Brass                                                                                                                      |
| Material housing                    | Steel                                                                                                                      |
| Material screen                     | PS                                                                                                                         |
| Housing colour                      | Silver                                                                                                                     |

| Feature        | Value                                                                         |
|----------------|-------------------------------------------------------------------------------|
| Product weight | 80 g                                                                          |
| Scale          | Triple scale<br>MPa (outer scale)<br>Bar (outside scale)<br>psi (inner scale) |