

# Solenoid valve

## JMUH-5/2-D-1C-VI



Part number: 119665

FESTO

For valve terminal

This type is suitable for vacuum.

Products to be discontinued. Available until 2011.



## Data sheet

Feature	Value
Valve function	5/2 monostable
Width	42 mm
Operating pressure	-0.9 ... 8 bar
Design structure	Piston slide
Type of reset	mechanical spring
Nominal size	9.5 mm
Sealing principle	soft
Manual override	Pushing
Type of piloting	direct
Flow direction	non reversible
Operating medium	filtered compressed air, grade of filtration 40 µm, lubricated or unlubricated
Medium temperature	-5 ... 50 °C
Ambient temperature	-5 ... 50 °C
Mounting type	with through hole
Pneumatic connection, port 1	Connection plate size 2 as per ISO 5599-2
Pneumatic connection, port 2	Connection plate size 2 as per ISO 5599-2
Pneumatic connection, port 3	Sub-base
Pneumatic connection, port 4	Connection plate size 2 as per ISO 5599-2
Pneumatic connection, port 5	Sub-base