

Throttle plate GRO-ZP-3-ISO

Part number: 119674

FESTO



Data sheet

Feature	Value
Valve function	Flow control function
Operating pressure	0 bar...16 bar
Standard nominal flow rate (standardised to DIN 1343)	1500 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:...]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Media temperature	-20 °C...80 °C
Ambient temperature	-20 °C...80 °C
Type of mounting	With through-hole