

Silencer
AMTE-M-LH-N18
Part number: 1206989

FESTO



Data sheet

Feature	Value
Mounting position	optional
Size of pack	20
Operating pressure	0 MPa...1 MPa 0 bar...10 bar
Flow rate to atmosphere	1615 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Sound pressure level	77 dB(A)
Ambient temperature	-40 °C...80 °C
Product weight	9 g
Pneumatic connection	1/8 NPT
Material shock absorber insert	Bronze
Material screwed plug	Brass
Note on materials	RoHS-compliant