

Coupling
EAMC-42-50-12-16
Part number: 1232880



Data sheet

Feature	Value
Mounting diameter 1	12 mm
Mounting diameter 2	16 mm
Size	42
Nominal length	50 mm
Mounting position	optional
Max. rotational speed	6000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	34.8 kgmm ²
Transmittable torque	17 Nm
Product weight	140 g
Note on materials	RoHS-compliant