

Push-in L-fitting NPQP-LQ-R38-Q12-FD-P10

Part number: 133069

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal size	6.9 mm
Design	T-shape, additional push-in connector, lengthwise Push-pull principle
Size of pack	10
Temperature-dependent operating pressure	-0.95 bar...10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:~:]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Suitable for use with food	See supplementary material information
Ambient temperature	-20 °C...60 °C
Product weight	26 g
Type of mounting	External hexagon, size 22 mm
Pneumatic connection, port 1	Male thread R3/8
Pneumatic connection, port 2	For tubing outer diameter of 12 mm
Note on materials	RoHS-compliant
Material housing	PP
Material tubing clamp component	High-alloy stainless steel