


Suction cup complete VAS-125-3/8-PUR-B

Part number: 1396108

FESTO



Data sheet

Feature	Value
Height compensator for suction cup	6 mm
Nominal size	7 mm
Suction cup diameter	125 mm
Suction cup volume	79.1 cm ³
Effective suction diameter	101.8 mm
Position of connection	Top
Mounting position	optional
Suction cup shape	Round, flat
Operating pressure	-0.095 MPa...0 MPa -0.95 bar...0 bar -13.775 psi...0 psi
Nominal operating pressure	-0.07 MPa -0.7 bar -10.15 psi
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::-]
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-20 °C...60 °C
Holding force at nominal operating pressure	570 N
Product weight	249 g
Type of mounting	Via vacuum port
Vacuum connection	G3/8
Colour	Blue
Shore hardness	60 +/- 5
Material screwed plug	Die-cast zinc
Note on materials	RoHS-compliant
Material suction cup	PUR