


Coupling
EAMD-25-22-10-10X12
Part number: 1453860

FESTO



Data sheet

Feature	Value
Mounting diameter 1	10 mm
Mounting diameter 2	10 mm
Size	25
Nominal length	22 mm
Mounting position	optional
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	3.2 kgmm ²
Transmittable torque	9 Nm
Product weight	43.7 g
Note on materials	RoHS-compliant