


axial kit
EAMM-A-F28-60H
Part number: 1454252



Suitable for electric drives.



Data sheet

Feature	Value
Assembly position	Any
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	8.2 Nm
Product weight	370 g
Interface code, actuator	F28
Interface code, motor in	60H
Materials note	Conforms to RoHS