

MFH-3-1/4-NA

Solenoid valve

Data sheet

Part no.: 150716

Page:1

Feature	Data/description
Switching function short code	3/2
Control type	Monostable
Operating pressure min.	2 bar
Operating pressure max.	10 bar
Type of connection, air supply	Female thread
Connecting thread, supply port	G 1/4
Air connection type power port	Sub-base
Type of connection, exhaust	Female thread
Connecting thread, exhaust port	G 1/4
Country-specific approval certificate (U	UL(OL)