

Elbow fitting
LJK-1/8-I/I
Part number: 151784



Data sheet

Feature	Value
Mounting position	optional
Operating pressure	-0.95 bar...8 bar
Operating medium	Compressed air to ISO 8573-1:2010 [-:~:-]
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Product weight	25 g
Suction cup mounting	G1/8
Vacuum connection	G1/8