

Push-in sleeve QSH-3/16-U

Part number: 153818

FESTO



Data sheet

Feature	Value
Size	Standard
Mounting position	optional
Design	Straight design Push-pull principle
Size of pack	1
Operating pressure complete temperature range	-0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi
Maritime classification	See certificate
Operating medium	Compressed air to ISO 8573-1:2010 [7:::]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C 14 °F...140 °F
Product weight	1 g
Pneumatic connection, port 1	Push-in sleeve Ø 3/16"
Pneumatic connection, port 2	Push-in sleeve Ø 3/16"
Colour of release ring	grey
Note on materials	RoHS-compliant
Material housing	PBT