

Parallel kit
EAMM-U-60-D32-42B/C-91
Part number: 1577393

FESTO



Data sheet

Feature	Value
Size	60
Mounting position	optional
Gear unit ratio	1:1
Max. rotational speed	6000 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	26.7 kgmm ²
Frictional torque independent of load	0.07 Nm
Transmittable torque	3 Nm
Product weight	1100 g
Interface code, actuator	D32B
Interface code, motor in	42B 42C
Note on materials	RoHS-compliant