

Sensor tester SM-TEST-1

Part number: 158481

FESTO



Data sheet

Feature	Value
CE mark (see declaration of conformity)	To EU EMC Directive
Ambient temperature	0 °C...40 °C
Operational voltage range DC	12 V...20 V
Power supply	Two 9 V block batteries
Ready status indication	Green LED
Degree of protection	IP20
LABS (PWIS) conformity	VDMA24364-B2-L