


Connecting cable KMP1-02-VI-12-X

Part number: 158986

FESTO

The cable is available in lengths from 1 to 99 m.



Exemplary representation

Data sheet

Feature	Value
Assembly position	Any
Operating voltage range AC	$\leq 300\text{ V}$
Operating voltage range DC	$\leq 250\text{ V}$
Permissible current load	4 A
Protection class	IP65
Ambient temperature	5 ... 70 °C -30 ... 70 °C
Electrical connection	25-pin Plug socket
Cable structure	25 x 0,75 mm ²
Cable diameter	13 mm
Mounting type	With clamp strap
Materials information, housing	Die-cast light alloy
Materials information, cable sheaths	PE
Material information for crimp connectors	Copper alloy Silver plated