

Air reservoir CRVZS-0.4

Part number: 160234

FESTO



Data sheet

Feature	Value
Volume	0.4 l
Mounting position	optional
Conforms to standard	AD 2000
Operating pressure	-0.095 MPa...1.6 MPa -0.95 bar...16 bar -13.78 psi...232 psi
Approval	CRN German Technical Control Board (TÜV)
Certificate issuing authority	TSSACRN0H17477.5C
Operating medium	Compressed air to ISO 8573-1:2010 [-:::-] Nitrogen
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitable for use with food	See supplementary material information
Media temperature	-10 °C...100 °C
Ambient temperature	-10 °C...100 °C
Max. tightening torque for connecting thread	23 Nm
Product weight	543 g
Type of mounting	Via fixing clips
Pneumatic connection	G1/4
Note on materials	RoHS-compliant
Material air reservoir	High-alloy stainless steel
Material fixing clips	High-alloy stainless steel