

Air reservoir CRVZS-2

Part number: 160236

FESTO



Data sheet

Feature	Value
Volume	2 l
Mounting position	optional
Conforms to standard	AD 2000
Operating pressure	-0.095 MPa...1.6 MPa -0.95 bar...16 bar -13.78 psi...232 psi
Approval	CRN German Technical Control Board (TÜV)
Certificate issuing authority	TSSACRN0H17477.5C
Operating medium	Compressed air to ISO 8573-1:2010 [-:::] Nitrogen
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitable for use with food	See supplementary material information
Media temperature	-10 °C...100 °C
Ambient temperature	-10 °C...100 °C
Max. tightening torque for connecting thread	55 Nm
Product weight	1681 g
Type of mounting	With through-hole
Pneumatic connection	G1/2
Note on materials	RoHS-compliant
Material air reservoir	High-alloy stainless steel