

Filter

LF-1-D-5M-MAXI-A

Part number: 162625

FESTO



Data sheet

Feature	Value
Size	Maxi
Series	D
Mounting position	Vertical +/-5°
Grade of filtration	5 µm
Condensate drain	Fully automatic
Design	Sintered filter with centrifugal separator
Bowl guard	Metal bowl guard
Operating pressure	2 bar...12 bar
Standard nominal flow rate (standardised to DIN 1343)	3800 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:9:-] Inert gases
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
Air purity class at output	Compressed air to ISO 8573-1:2010 [6:8:4] Inert gases
Media temperature	5 °C...60 °C
Ambient temperature	5 °C...60 °C
Product weight	1440 g
Type of mounting	In-line installation With accessories
Pneumatic connection, port 1	G1
Pneumatic connection, port 2	G1
Note on materials	RoHS-compliant
Material filter	PE
Material housing	Die-cast zinc
Material bowl	PC