

Silencer U-M3

Part number: 163978

★ Standard product range
Product to be discontinued

Type to be discontinued. Do not use for new projects. See Support
Portal for alternative products.

FESTO



Data sheet

| Feature | Value |
|---|---|
| Assembly position | Any |
| Operating pressure | 0 ... 10 bar |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Sound pressure level | 65 dB(A) |
| Ambient temperature | -10 ... 70 °C |
| Pneumatic connection | M3 |
| Materials information for silencer insert | Bronze |
| Materials information for screw-in stud | Brass |
| Materials note | Conforms to RoHS |