

Fibre-optic cable
SOEZ-LLG-RT-0,5-M6X0,75
Part number: 165356



Data sheet

Feature	Value
Measurement method	Light guide Diffuse sensor
Ambient temperature	-20 °C...160 °C
Size	M6x0.75
Product weight	34 g
Material housing	Brass Chrome-plated
Setting range upper limit	100 mm
Ambient temperature with moving installation	-20 °C...120 °C
Degree of protection	IP54
LABS (PWIS) conformity	VDMA24364-B2-L