


Axis interface SPC-AIF-POT

Part number: 170228

FESTO

For potentiometer



Data sheet

Feature	Value
Max. proportional valve current consumption	1.1 A
Typical axis interface current consumption	100 mA
CE mark (see declaration of conformity)	to EU directive for EMC
Continuous shock resistance per DIN/IEC 68, parts 2 - 82	Tested in accordance with severity level 2
Protection class	IP65 to IEC 60529
Vibration resistance per DIN/IEC 68, parts 2 - 6	Tested in accordance with severity level 2
Ambient temperature	0 ... 50 °C
Product weight	300 g
Electrical connection, proportional valve	Plug Round design M9 7-pin
Electrical connection, displacement encoder	Design A Cable with plug to DIN 43650 Cubic design
Electrical connection, AIF IN	Plug Round design M9 5-pin
Electrical connection, AIF OUT	Plug socket Round design M9 5-pin
Cable length	0.3 m