

# Connecting cable KSPC-AIF-1-WD-5

Part number: 170236

FESTO

For controller axis interface.



## Data sheet

Feature	Value
Operating voltage range AC	$\leq 60$ V
CE mark (see declaration of conformity)	to EU directive for EMC
Protection class	IP20
Ambient temperature with flexible cable installation	-5 ... 80 °C
Ambient temperature	-20 ... 70 °C
Product weight	266 g
Electrical connection 1	Angled socket, M9, 5-pin, screened
Electrical connection 2	Socket strip 5-pin
Cable structure	2x0,25 mm <sup>2</sup> + 2x0,34mm <sup>2</sup> +0,49mm <sup>2</sup>
Cable diameter	5.5 mm
Cable length	5 m
Housing colour	Black
Cable sheath colour	light grey
Materials information for locknut	Nickel-plated brass
Materials note	Conforms to RoHS
Materials information, housing	PA-reinforced PBT TPE-U(PUR)
Materials information, cable sheaths	TPE-U(PUR)
Material information for crimp connectors	Gold-plated bronze Copper alloy, tinned