

Plug socket MSSD-C-4P

Part number: 171157

FESTO



Data sheet

Feature	Value
Type of mounting	On solenoid valve via M3 central screw
Mounting position	optional
Product weight	22 g
Electrical connection	3-pin Angled socket Type A To DIN EN 175301-803 Square design MSC Square design MSN1
Cable fitting	Pg 9
Cable diameter	6 mm...8 mm
Nominal cross section conductor	1.5 mm²
Degree of protection	IP65
Ambient temperature	-25 °C...90 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Material housing	Polymer
Housing colour	Black