


Axial kit
EAMM-A-P4-28B-28A
Part number: 1731466



Data sheet

Feature	Value
Nominal length	12 mm
Mounting position	optional
Max. rotational speed	10000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	0.28 kgmm ²
Transmittable torque	0.7 Nm
Product weight	40 g
Interface code, actuator	P4-28B
Interface code, motor in	28A
Interface code, clutch housing	28B
Note on materials	RoHS-compliant