

Suction cup VAS-10-M5-SI

Part number: 173442

FESTO

Sealing ring is not included in the scope of delivery.
Type to be discontinued. Available until 2012.



Data sheet

Feature	Value
Nominal size	2 mm
suction cup diameter	10 mm
Effective suction diameter	8 mm
Design structure	Vacuum connection at top round, standard
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Ambient temperature	-40 ... 200 °C
Breakaway force at 70% vacuum	4.5 N
Product weight	3 g
Mounting thread	M5
suction cup mounting	M5
Vacuum connection	M5
Shore hardness	60 +/- 5
Materials information for screw-in stud	Wrought Aluminium alloy
Materials note	Contains PWIS substances
Materials information for suction cup	VMQ (silicon)