

Service unit FRC-3/4-D-7-MAXI-NPT

Part number: 173882

FESTO



Data sheet

Feature	Value
Size	Maxi
Mounting position	Vertical
Condensate drain	Manually rotating
Grade of filtration	40 µm
Operating pressure	0.1 MPa...1.6 MPa 1 bar...16 bar
Pressure regulation range	0.5 bar...7 bar
Max. pressure hysteresis	0.04 MPa 0.4 bar 5.8 psi
Standard nominal flow rate (standardised to DIN 1343)	8500 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [-:::-]
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Product weight	2390 g
Type of mounting	In-line installation Via mounting bracket Either:
Pneumatic connection, port 1	3/4 NPT
Pneumatic connection, port 2	3/4 NPT
Material housing	Die-cast zinc
Material bowl	PC