

Service unit FRC-1-D-MAXI-NPT

Part number: 173884

FESTO



Data sheet

Feature	Value
Size	Maxi
Mounting position	Vertical
Condensate drain	Manually rotating
Grade of filtration	40 µm
Operating pressure	0.1 MPa...1.6 MPa 1 bar...16 bar
Pressure regulation range	0.5 bar...12 bar
Max. pressure hysteresis	0.04 MPa 0.4 bar 5.8 psi
Standard nominal flow rate (standardised to DIN 1343)	8500 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [:-9:-] Inert gases
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Air purity class at output	Compressed air to ISO 8573-1:2010 [7:8:-] Inert gases
Media temperature	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Product weight	2520 g
Type of mounting	In-line installation Via mounting bracket Either:
Pneumatic connection, port 1	1 NPT
Pneumatic connection, port 2	1 NPT
Note on materials	RoHS-compliant
Material housing	Die-cast zinc
Material bowl	PC