

Coupling
EAMC-65-90-25-32
Part number: 1745817

FESTO



Data sheet

Feature	Value
Mounting diameter 1	25 mm
Mounting diameter 2	32 mm
Size	65
Nominal length	90 mm
Mounting position	optional
Max. rotational speed	4500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	417 kgmm ²
Transmittable torque	92 Nm
Product weight	535 g
Note on materials	RoHS-compliant