

Swivel flange SNCB-40-R3

Part number: 176945

FESTO



Data sheet

| Feature | Value |
|--|---|
| Size | 40 |
| Based on standard | ISO 15552 |
| Variants | High corrosion protection |
| Corrosion resistance class CRC | 3 - high corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Suitability for the production of Li-ion batteries | Metals with more than 5% by mass of copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils |
| Ambient temperature | -40 °C...90 °C |
| Max. load capacity | 1.5 kN |
| Product weight | 151 g |
| Note on materials | RoHS-compliant |
| Material mounting | Die-cast aluminium With protective coating |
| Material bolt | High-alloy stainless steel |
| Material bearing | Polymer |
| Material disc | Galvanised steel |
| Material screws | High-alloy stainless steel |
| Material lock | Spring steel, galvanised |