

# Multi-pin plug distributor MPV-E/A12-M8

Part number: 177670

FESTO



## Data sheet

Feature	Value
Type of mounting	Either: With through-hole With H-rail
Product weight	120 g
Electrical connection system I/Os	M8 3-pin
Operational voltage range DC	10 V...30 V
Max. current per plug-in position	1 A
Permissible current load	4 A
Degree of protection	IP65 In assembled state To IEC 60529
Ambient temperature	-20 °C...80 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Material housing	PA6 reinforced
Material socket	Brass