

Plug socket with cable KMEB-2-24-M12-0,5-LED

Part number: 177677

FESTO



Data sheet

Feature	Value
Switching position indicator	LED
Type of mounting	On solenoid valve via M2.5 central screw
Mounting position	optional
Electrical connection	5-pin Angled socket Type C To DIN EN 175301-803
Nominal operating voltage DC	24 V
Protective conductor connection	Available
Cable length	0.5 m
Cable diameter	4.6 mm
Cable structure	3 x 0.5 mm ²
Degree of protection	IP65 To IEC 60529
Ambient temperature	-5 °C...50 °C
CE mark (see declaration of conformity)	In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B2-L
Material cable sheath	TPE-U(PU)
Cable sheath colour	Black
Material housing	PA POM
Housing colour	Transparent
Material electrical contact	Bronze