

# Plastic tubing PUN-10X1,5-GN

Part number: 178427

FESTO



## Data sheet

| Feature                                       | Value                                                                                                                                                                                  |
|-----------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Outside diameter                              | 10 mm                                                                                                                                                                                  |
| Flow-relevant bending radius                  | 54 mm                                                                                                                                                                                  |
| Inside diameter                               | 7 mm                                                                                                                                                                                   |
| Min. bending radius                           | 28 mm                                                                                                                                                                                  |
| Instructions on use                           | TPE-U Ester based<br>The plastic tubing can only be installed in contact with cables if the sheathing is free of phosphoric acid esters. Otherwise the plastic tubing may get damaged. |
| Tubing characteristics                        | Suitable for energy chains                                                                                                                                                             |
| Operating pressure complete temperature range | -0.095 MPa...0.7 MPa<br>-0.95 bar...7 bar<br>-13.775 psi...101.5 psi                                                                                                                   |
| Temperature-dependent operating pressure      | -0.095 MPa...1 MPa<br>-0.95 bar...10 bar<br>-13.775 psi...145 psi                                                                                                                      |
| Approval                                      | German Technical Control Board (TÜV)                                                                                                                                                   |
| Certificate issuing authority                 | B 013277 0506 00                                                                                                                                                                       |
| Operating medium                              | Compressed air to ISO 8573-1:2010 [7:-:-]                                                                                                                                              |
| Fire test material                            | UL94 HB                                                                                                                                                                                |
| LABS (PWIS) conformity                        | VDMA24364-B2-L                                                                                                                                                                         |
| Ambient temperature                           | -35 °C...60 °C                                                                                                                                                                         |
| Product weight according to length            | 0.0489 kg/m                                                                                                                                                                            |
| Pneumatic connection                          | For push-in connector O.D. 10 mm                                                                                                                                                       |
| Colour                                        | Green                                                                                                                                                                                  |
| Shore hardness                                | D 52 +/-3                                                                                                                                                                              |
| Note on materials                             | RoHS-compliant                                                                                                                                                                         |
| Material tubing                               | TPE-U(PU)                                                                                                                                                                              |