

Sensor bracket
DASI-Q11-50-A-SR
Part number: 1797071

FESTO



Data sheet

Feature	Value
Size	50
Design	For T-slot Sensor rail
For piston diameter	Ø50
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Product weight	75 g
Type of mounting	Clamped in T-slot Via through-hole and screw Via slot nuts
Note on materials	RoHS-compliant
Material screws	Steel Galvanised