

Plug socket NTSD-GD-9

Part number: 18493

FESTO



Data sheet

Feature	Value
Type of mounting	Via union nut
Mounting position	optional
Product weight	25 g
Electrical connection	4-pin Straight socket Screw terminal
Operational voltage range AC	250 V
Permissible current load	16 A
Cable fitting	Pg 9
Permissible cable diameter	6 mm...8 mm
Connection cross section	1.5 mm ²
Degree of protection	IP67
Ambient temperature	-5 °C...50 °C
Storage temperature	-20 °C...70 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Material housing	PBT
Material electrical contact	Copper alloy Brass