


Branching module FRM-1/4-D-MIDI

Part number: 186523

FESTO



Data sheet

Feature	Value
Mounting position	optional
Design	Branching module
Operating pressure	0 MPa...1.6 MPa 0 bar...16 bar
Standard nominal flow rate in main flow direction 1->2	3300 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-] Inert gases
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
Air purity class at output	Compressed air to ISO 8573-1:2010 [7:-:-] Inert gases
Media temperature	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Product weight	532 g
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4
Pneumatic connection, port 3	G1/2
Pneumatic connection, port 4	G1/4
Note on materials	RoHS-compliant
Material housing	Die-cast zinc