


Cable distributor
ASI-KVT-FK
Part number: 18786



Data sheet

Feature	Value
Type of mounting	With through-hole
Mounting position	optional
Product weight	7.2 g
Operational voltage range DC	75 V
Operational voltage range AC	60 V
Permissible current load	3 A
Connection cross section	1.5 mm ²
Degree of protection	IP65
Ambient temperature with moving cable	-5 °C...50 °C
Storage temperature	-30 °C...85 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Material housing	PA
Material electrical contact	Bronze