

# Suction gripper ESG-60

Part number: 189177

FESTO



## Data sheet

| Feature                           | Value                                                                                                |
|-----------------------------------|------------------------------------------------------------------------------------------------------|
| Suction cup diameter              | 60 mm                                                                                                |
| Mounting position                 | Vertical                                                                                             |
| Design                            | Vacuum port on top<br>Vacuum port on side<br>With height compensator<br>With long height compensator |
| Correlation to suction-cup holder | Size 5                                                                                               |
| Suction cup shape                 | Round extra deep<br>Round, flat<br>Round deep                                                        |
| Operating medium                  | Atmospheric air based on ISO 8573-1:2010 [7:::-]                                                     |
| Corrosion resistance class CRC    | 1 - Low corrosion stress                                                                             |
| Ambient temperature               | -30 °C...200 °C                                                                                      |
| Vacuum connection                 | G1/8<br>G1/4                                                                                         |
| Note on materials                 | RoHS-compliant                                                                                       |
| Material suction cup              | FPM<br>NBR<br>PUR<br>VMQ (silicone)<br>Vulkollan                                                     |