

Suction cup complete holder ESH-HD-3-QS

Part number: 189237

FESTO



Data sheet

Feature	Value
Height compensator for suction-cup holder	6 mm
Nominal size	3.3 mm
Volume	0.573 cm ³
Mounting position	Vertical
Design	Vacuum port on side With height compensator
Correlation to suction-cup holder	Size 3
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	0 °C...60 °C
Product weight	46 g
Type of mounting	Via lock nut
Suction cup mounting	M4
Vacuum connection	QS-6
Note on materials	RoHS-compliant
Material seals	NBR Steel
Material retaining bracket	Aluminium Nickel-plated brass POM Tempered steel High-alloy steel