

Suction cup complete holder

ESH-HD-6-G

Part number: 189242

FESTO



Data sheet

Feature	Value
Height compensator for suction-cup holder	20 mm
Nominal size	10 mm
Volume	13.171 cm ³
Mounting position	Vertical
Design	Vacuum port on side With height compensator
Correlation to suction-cup holder	Size 6
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-10 °C...60 °C
Product weight	472 g
Type of mounting	Via lock nut
Suction cup mounting	M20x2
Vacuum connection	G1/4
Note on materials	RoHS-compliant
Material retaining bracket	Aluminium Nickel-plated brass POM Tempered steel High-alloy steel