

Suction cup complete holder

ESH-HDL-2-PK

Part number: 189246

FESTO



Data sheet

Feature	Value
Height compensator for suction-cup holder	10 mm
Nominal size	2.2 mm
Volume	0.138 cm ³
Mounting position	Vertical
Design	Vacuum port on side With height compensator
Correlation to suction-cup holder	Size 2
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-10 °C...60 °C
Product weight	32 g
Type of mounting	Via lock nut
Suction cup mounting	Diameter 4 mm
Vacuum connection	PK-4
Note on materials	RoHS-compliant
Material seals	NBR Steel
Material retaining bracket	Aluminium Nickel-plated brass POM Tempered steel High-alloy steel