

Suction cup complete holder ESH-HE-3-G1/8

Part number: 189255

FESTO



Data sheet

Feature	Value
Nominal size	3 mm
Volume	0.106 cm ³
Mounting position	optional
Design	Vacuum port on top
Correlation to suction-cup holder	Size 3
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-10 °C...60 °C
Product weight	11 g
Type of mounting	Via male thread Via vacuum port
Suction cup mounting	M4
Vacuum connection	G1/8
Note on materials	RoHS-compliant
Material seals	Wrought aluminium alloy NBR POM Steel
Material retaining bracket	Tempered steel