

Suction cup complete ESS-4-SNA

Part number: 189273

FESTO



Data sheet

Feature	Value
Min. workpiece radius	10 mm
Nominal size	1.2 mm
Suction cup diameter	4 mm
Suction cup volume	0.008 cm ³
Suitable for ejector pulse	4 bar
Position of connection	Top
Mounting position	optional
Special characteristics	Antistatic
Correlation to suction-cup holder	Size 1
Suction cup shape	Round, flat
Operating pressure	-95 kPa...0 kPa -0.95 bar...0 bar -13.775 psi...0 psi
Nominal operating pressure	-70 kPa -0.7 bar -10.15 psi
Surface resistance	200 Ohm
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Suitable for use with food	See supplementary material information
Ambient temperature	-10 °C...70 °C
Holding force at nominal operating pressure	0.46 N
Lateral force at nominal operating pressure	0.5 N
Product weight	0.1 g
Type of mounting	Via vacuum port
Vacuum connection	Outside diameter 3 mm
Colour	Black/white dot
Shore hardness	50 +/- 5
Material screwed plug	Nickel-plated brass
Note on materials	RoHS-compliant

Feature	Value
Material suction cup	NBR