

Suction cup complete ESS-30X90-ON

Part number: 189418

FESTO



Data sheet

Feature	Value
Nominal size	6 mm
Suction cup size	30x90 mm
Suction cup volume	10.17 cm ³
Position of connection	Top
Mounting position	optional
Correlation to suction-cup holder	Size 5
Suction cup shape	Oval, flat
Operating pressure	-95 kPa...0 kPa -0.95 bar...0 bar -13.775 psi...0 psi
Nominal operating pressure	-70 kPa -0.7 bar -10.15 psi
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Suitable for use with food	See supplementary material information
Ambient temperature	-10 °C...70 °C
Holding force at nominal operating pressure	134.4 N
Horizontal lateral force at nominal operating pressure	201 N
Vertical lateral force at nominal operatin pressure	134.5 N
Product weight	55.3 g
Type of mounting	Via vacuum port
Vacuum connection	M10
Colour	Black
Shore hardness	50 +/- 5
Note on materials	RoHS-compliant
Material suction cup	NBR