


Suction cup without connector

ESV-40-BN

Part number: 191060

FESTO



Data sheet

Feature	Value
Height compensator for suction cup	9.5 mm
Min. workpiece radius	90 mm
Suction cup diameter	40 mm
Suction cup volume	11.699 cm ³
Position of connection	Top
Mounting position	optional
Suction cup shape	Round bellows 1.5 convolutions
Operating pressure	-95 kPa...0 kPa -0.95 bar...0 bar -13.775 psi...0 psi
Nominal operating pressure	-70 kPa -0.7 bar -10.15 psi
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::]
LABS (PWIS) conformity	VDMA24364-A1-L
Suitable for use with food	See supplementary material information
Ambient temperature	-10 °C...70 °C
Holding force at nominal operating pressure	52.3 N
Product weight	9.8 g
Colour	Black
Shore hardness	50 +/- 5
Note on materials	RoHS-compliant
Material suction cup	NBR