

Stop element
YSRWJ-5-8-A
Part number: 192968

FESTO



Data sheet

Feature	Value
Size	5
Stroke	8 mm
Cushioning	Self-adjusting Soft characteristic curve
Mounting position	optional
Fine adjustment	0.03 mm
Position detection	Via proximity switch
Max. impact speed	2 m/s
Reset time at room temperature	0.2 s
Reset time at min. ambient temperature	1 s
Mode of operation	Pushing Single-acting
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C...60 °C
Cushioning length	8 mm
Max. stop force	200 N
Max. energy consumption per stroke	1 J
Max. energy consumption per hour	10000 J
Max. residual energy	0.01 J
Reset force	1 N
Product weight	45 g
Type of mounting	Via lock nut
Material seals	NBR
Material housing	Brass Nickel-plated
Material piston rod	High-alloy steel