

Manifold block MHP1-PR4-3

Part number: 197192

FESTO



Data sheet

| Feature | Value |
|------------------------------------|--|
| Max. number of valve positions | 4 |
| Operating pressure | 0 bar...8 bar |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -10 °C...60 °C |
| Mounting method for sub-base | With through-hole |
| Mounting method for valve | Via female thread |
| Pneumatic connection, port 1 | M7 |
| Pneumatic connection, port 3 | M7 |
| Material sub-base | Wrought aluminium alloy |