

Clevis foot
CRLMC-50
Part number: 197322



Data sheet

Feature	Value
Size	50
Based on standard	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Mounting position	optional
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C...80 °C
Product weight	254 g
Note on materials	RoHS-compliant
Material mounting	Electropolished High-alloy steel
Material bearing	Polymer