

Clevis foot CRLMC-100

Part number: 197325

FESTO



Data sheet

Feature	Value
Size	100
Based on standard	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Mounting position	optional
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C...80 °C
Product weight	722 g
Note on materials	RoHS-compliant
Material mounting	Electropolished High-alloy steel
Material bearing	Polymer