

Silencer UO-M7

Part number: 197582

FESTO



Data sheet

Feature	Value
Mounting position	optional
Design	Open silencer
Operating pressure	0 MPa...0.8 MPa 0 bar...8 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Product weight	2.5 g
Pneumatic connection	M7
Material shock absorber insert	PE
Material screwed plug	PE
Note on materials	RoHS-compliant