

Spiral plastic tubing PUN-10X1,5-S-1-BL

Part number: 197596

FESTO



Data sheet

Feature	Value
Working length	1 m
Outside diameter	10 mm
Block length	0.305 m
Inside diameter	7 mm
Winding diameter	80 mm
Number of turns	9.5
Temperature-dependent operating pressure	-0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi
Approval	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0506 00
Operating medium	Compressed air to ISO 8573-1:2010 [7::-]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-35 °C...60 °C
Product weight	110 g
Pneumatic connection	For push-in connector O.D. 10 mm
Colour	Blue
Shore hardness	D 52 +/-3
Material tubing	TPE-U(PU)